

Fast & Simple Recharging Process

Warranty & Return Policy



Recharging Directions



Step A: When output water quality has exceeded pre-determined level, or when spotting occurs, DI water is no longer being produced. Shut off water supply and remove tank head.



Step B: Empty resin into a waste container and rinse out tank. Dispose in accordance with federal, state, and local regulations.



Step C: Return distributor tube into the tank and place rubber cap over top of tube. Place funnel into top of the tank.



Step D: Slowly pour or scoop resin into tank. Shake or tap tank to get all of the resin bedded. Lastly, finish filling the unit with resin to within 2 inches of the top.



Step E: Remove funnel and rubber cap. Replace tank head. Make sure all o-rings are properly seated. Ensure seating areas are free from foreign material, apply silicone lubricant to surface of o-rings.



Step F: Turn on water supply. You are ready to produce mineral-free water!

On The Go® One (1) Year Limited Warranty

The On The Go® Portable Water Softener, LLC (Company) makes every effort to assure that its products meet high quality standards, and warrants to the original purchaser (User) that Product is free from defects in materials and workmanship for a period of one year from the date of purchase. This warranty does not apply to damage due directly or indirectly to misuse, abuse, negligence, or accidentals; repairs or alterations outside our facility; or to lack of maintenance. The Company shall in no event be liable for death, injuries to persons or property, or for incidental, and contingent, special or consequential damages arising from the use of the Product.

In the event User believes Product to be defective, User shall return Product to Company. Proof of purchase showing date of purchase and an explanation of the complaint must accompany Product. If after inspection, Company determines Product to be defective, Company at its discretion may elect to repair or replace Product including shipping and handling expenses. If Company cannot, however, readily and quickly replace Product, Company will refund User Product's purchase price. In the event, however, after inspection Company determines Product became damaged due to User's misuse or due to any cause whatsoever which is outside the scope of the warranty, then User shall bear any shipping and handling cost related to Product. Although this warranty gives User specific legal rights, it does not replace other rights that User may have which vary from state to state.

If any event no legal action, regardless of its form, arising out of the use of the Product shall be brought more than a year after its occurrence.

The Road Wave RV Pressure Washer System Limited Warranty

This product is under warranty to the original retail consumer against defects in material and workmanship for a period of 1 (one) year on machine, 90 days on gun and hose assembly, from the date of retail purchase and is not transferable. Warranty covers replacement parts. This limited one year warranty applies only to products used in consumer applications and does not apply to rental or commercial applications.

Items returned for warranty consideration must have a Returned Merchandise Authorization (RMA) number. All unauthorized returns will be refused and shipped back to sender. Call The Road Wave Monday through Friday 8:00 a.m. - 5:00 p.m. (Mountain Standard Time). Or E-Mail to: Support@theroadwave.com 24 hours a day.

Mixed-Bed Standard Model



Double Standard Mixed Bed and Road Wave Model



Dual-Bed Standard Model



3905 W Roll Avenue
Bloomington, Indiana 47403
www.portablewaterDI.com

TEL: 1-866-482-9614 • FAX: 1-260-482-9613



Refill DI resin kits are available by calling On The Go® or ordering via our website.

*Mixed-Bed Standard Model Refill Kit

Replacement Kits

www.portablewaterdi.com




The Original ON-BOARD RV Pressure Washer System

No More Searching For a
Place to Wash Your
RV & Tow Car

The SIMPLE Way to
a SPOT-FREE Rinse...



Pressure: 1350 Max PSI
Pump: 1.9 HP (2000 Hrs)
Power: 15 Amps
Induction Motor: 120v 60Hz
Washing Power: 1.9 GPM
Dimensions: 10W X 13L X 23H



- 50' Hose Reel
- Hot or Cold Water
- 2 Piece Gun with Adjustable Nozzle
- Soap Injector Tube and Filter
- Industrial Grade Metal Frame/Hose Reel
 - Standard Hose Connections
 - Recharging is Easy
- No Need to Towel Dry After Wash
- Save Time and Labor

Safety, Convenience, Quality
Built to last, The Road Wave is ideal
for Toy Haulers or anyone who wants
a safer experience on the road or at
the races.



Anytime! Anywhere!

Specifications:

Mixed-Bed Standard Model

Size: 22" X 6.75"
Weight: 18 lbs.
*Gallons: Approx. 280 Gallons Between Resin Change Outs
Warranty: Tank - 5 Years & Head - 1 Year
TDS Meter: Portable Hand Held TDS Meter
Flow Rate: Less than 2 gallon/minute for best performance & effectiveness



Double Standard Mixed Bed Model

Size: 22" X 9.5"
Weight: 32 lbs.
*Gallons: Approx. 560 Gallons Between Resin Change Outs
Warranty: Tank - 5 Years & Head - 1 Year
TDS Meter: Portable Hand Held TDS Meter
Flow Rate: Less than 2.5 gallon/minute for best performance & effectiveness



Dual-Bed Standard Model

Size: 22" X 6.5"
Weight: 18 lbs. each
*Gallons: Approx. 605 Gallons Between Resin Change Outs
Warranty: Tank - 5 Years & Head - 1 Year
TDS Meter: Portable Hand Held TDS Meter
Flow Rate: Less than 2 gallon/minute for best performance & effectiveness



*Basis of 200 ppm

The **capacity** of deionization systems is primarily determined by the Total Dissolved Solids (TDS) in the water source. The TDS can be measured by using the meter provided. The TDS can range from zero to 1000 PPM. The frequency for recharging is dependent upon the quality of the water source and the gallons used per application. Total organic compounds and chlorine in the water source can impact the capacity of the unit, but can be reduced by using a pre-carbon cartridge kit.

Best performance & effectiveness will be achieved by utilizing a power washer with two gallon or less per minute flow rate while using an adjustable fan-spray/mist application nozzle. Connection series: Water source - Deionizer - Power Washer - application nozzle.

www.portablewaterdi.com